

Rotating Module - Horizontal Axis DMH 200

Max. load 2,000 N manual operation



Advantages

- Rotating in both directions
- Safe indexing
- Rotating and indexing possible by one-hand operation
- Compact device
- Sturdy design for industrial assembly
- Allows ergonomic working
- Safe and quick handling in assembly processes
- 4 function variants
- Easily combinable with other modulog modules

modulog

Rotating module - horizontal axis DMH 200



Part no. 650X0XXXXX

Technical characteristics

Max. load: 2,000 N

Max. torque:

axial: 800 Nm radial: 800 Nm Angle of rotation: 360°

Operations

Manual

Hand lever





Application

Rotating module for universal use in assembly and handling processes in the industry.

Principal use

- Gear assembly
- Motor assembly
- Pump construction
- Turning operations during product transfer

Material

Body: steel, black oxide Rotating plate: steel, black oxide Indexing mechanism: steel, hardened Bearing: steel, hardened

Description

The rotating module - horizontal axis DMH is a double supported rotation axis that can compensate high axial and radial forces. The angle of rotation in both directions is 360°. Due to special bearings it is insensitive to shocks and thrusts.

The design of the rotating module allows its integration in applications with light as well as with heavy loads.

When using the rotating module in assembly processes, component parts can be rotated rationally, quickly and safely and can be assembled ergonomically from all sides.

The rotating module is equipped with an optional indexing (see page 3 to 5).

Indexing

Operation with

- Hand lever
- Foot pedal



Combinable with the modules

• Tilting module KMB 100 as per data sheet M 2.101



 Rotating module – vertical axis DMV 600 as per data sheet M 1.301



 Lifting module as per data sheet M 4.XXX



Mounting

To fix modulog modules or components of the user, the rotating module has a 140 x 140 modulog interface in the flange plate and the body.

In addition, at the bottom of the body 4 fixing threads are provided to allow vertical mounting of the rotating module.

As accessory for the vertical mounting onto other *modulog* modules an adaptor plate with an 140 x 140 *modulog* interface is available.

As accessory for individual fixing holes a round flange plate without 140 x 140 interface is available.

Operation

The basic version of the rotating modules does not have any operating elements.

The rotating operation is manually effected at the workpiece or at the assembly fixture. Alternatively, versions with hand lever are available.

The indexing is operated by a hand lever of the rotating module or a separate hand lever or foot pedal.

modulog interfaces

• Flange plate: 140 x 140 - M10

• Body: 140 x 140 - Ø 10.5 mm

Accessories

• Adaptor plates as per data sheet M 8.110

 Flange plate as per data sheet M 8.120

manual operation



Description

The rotating module - horizontal axis DMH 200 does not have an indexing in its basic version. The rotating operation is manually effected at the workpiece or at the assembly fixture.

65050236O Part no.


Technical characteristics

manual at the Operation: component part

Angle of rotation: 360°

Direction of rotation: Indexing: both directions without Weight: 20 kg

Maximum admissible load



Maximum admissible forces:

 $F_X = \pm 2,000 \text{ N}$ $F_y = \pm 2,000 \text{ N}$ $F_{Z} = \pm 1,000 \text{ N}$


Total $M_{X/V} =$ 800 Nm

Maximum admissible torques

Mz: only relevant for version with indexing (see page 3 to 6)

In the case of eccentric loads, it is recommended to compensate these by counterweights. In offposition the indicated maximum torques may

The forces and torques have to be considered by the operator.



Accessories

Adaptor plate

for vertical mounting of the rotating module

Part no. 6311326

See data sheet M 8.110

• Flange plate

round for individual fixing holes

Part no. 6311400

See data sheet M 8.120

Important notes!

The fixing screws M10 are not included in our delivery.

The rotating module is designed for applications within closed rooms.

Subject to modifications

operation with hand lever



Description

The rotating module - horizontal axis DMH 200 with automatic indexing is a compact and functional unit.

Rotating as well as indexing are ergonomically operated by one hand lever only.

Operation

To rotate the component part the hand lever is operated in any direction.

Every 90° indexing of the position is made automatically. Engagement and disengagement of the indexing is also effected automatically.

The off-position of the hand lever can be engaged in steps of 90°, so that for every rotation the desired off-position can be adjusted.

The standard indexing and engagement positions of the hand lever are set to $4 \times 90^{\circ}$.

Part no. 65050136M

Technical characteristics

Operation: with hand lever
Angle of rotation: 360°
Direction of rotation: both directions
Indexing: mechanical, automatic

Operation with hand lever Indexing positions 4 x 90° Positioning precision < ±1°

Weight: 25 kg

Maximum admissible load


According to the version without indexing (see page 2).


Maximum admissible torque around the rotation axis $M_{\mbox{\scriptsize Z}}$


The maximum torque around the rotation axis of the rotating module M_Z in engaged mode is **250 Nm**.

The maximum torque to rotate the workpiece must not exceed **15 Nm**.

The module may only be moved in a controlled way to the indexing positions. If the indexing bolt engages in full motion, the module will be dynamically overloaded.







Accessories

Adaptor plate

for vertical mounting of the rotating module of the rotating module

Part no. 6311326

See data sheet M 8.110

Flange plate

round for individual fixing holes

Part no. 6311 400

See data sheet M 8.120

Important notes!

In case of vertical mounting of the rotating module - for example on a lifting module - it has to be considered that the hand lever can only be rotated by max. 270° in such applications. The fixing screws M10 are not included in our delivery. (Recommended property class 10.9) The rotating module is designed for applications within closed rooms.

Application example



Rotating module DMH 200, with adaptor plate vertically mounted on a lifting module.

M 1.101 / 1-21 E



Description

The rotating module - horizontal axis DMH 200 with actively operated indexing is a compact and functional unit.

Rotating as well as indexing are ergonomically operated by one hand lever only.

Operation

To unlock the indexing position the hand lever has to be tilted in axial direction by approx. 10° to get connected by form fit with the rotating module.

The component part can only be rotated in any direction by means of the hand lever. Only after safe locking in the desired position the hand lever is free again and the workpiece locked with the housing by form fit.

The off-position of the hand lever can be engaged in steps of 90°, so that for every rotation the desired off-position can be adjusted.

The standard indexing and engagement positions of the hand lever are set to $4 \times 90^{\circ}$.

Part no. 65050236M

Technical characteristics

Operation: with hand lever
Angle of rotation: 360°
Direction of rotation: both directions
Indexing: mechanical,
actively operated with
hand lever
Indexing positions 4 x 90°
Positioning precision < ±1°

Weight: 25 kg

Maximum admissible load

According to the version without indexing (see page 2)

Maximum admissible torque around the rotation axis $M_{\rm Z}$

The maximum torque around the rotation axis of the rotating module M_Z in engaged mode is **500 Nm**.

The maximum torque to rotate the workpiece must not exceed **20 Nm** due to ergonomic reasons.

The module may only be moved in a controlled way to the indexing positions. If the indexing bolt engages in full motion, the module will be dynamically overloaded.

Accessories

Adaptor plate

for vertical mounting of the rotating module of the rotating module

Part no. 6311326

See data sheet M 8.110

Flange plate

round for individual fixing holes


Part no. 6311 400

See data sheet M 8.120


Important notes!

In case of vertical mounting of the rotating module - for example on a lifting module - it has to be considered that the hand lever can only be rotated by max. 270° in such applications. The fixing screws M10 are not included in our delivery (recommended property class 10.9). The rotating module is designed for applications within closed rooms.

Dimensions



manual operation



128,5

Description

The rotating module - vertical axis DMH 200 with indexing with foot pedal is a compact and functional unit.

It consists of a basic module with integrated indexing mechanism and an operating unit with foot pedal, connected by a 2 m long hydraulic hose.

This flexible connection allows the individual placement of the operating unit at the most favourable ergonomic position.

The rotating operation is manually effected at the workpiece or at the assembly fixture.

Operation of the indexing

By operating the foot pedal by 35° downwards the index is released and the workpiece or the fixture can be rotated.

If the foot pedal is not operated, the index bolt engages automatically into the next indexing position.

The operation with a foot pedal guarantees that the operator always has both hands free.

The standard indexing positions are set to 8 x $45^{\circ},\,6\,x\,60^{\circ},\,4\,x\,90^{\circ}$ and $3\,x\,120^{\circ}.$ Other angles are available on request.

Important notes!

The fixing screws M10 are not included in our delivery (recommended property class 10.9).

The rotating module is designed for applications within closed rooms.

Code for part numbers

650802XXOI Part no.:

Engagement position

 $45 = 8 \times 45^{\circ}$

 $60 = 6 \times 60^{\circ}$

 $36 = 4 \times 90^{\circ}$

$12 = 3 \times 120^{\circ}$

Technical characteristics

Operation: manual at the component part

Angle of rotation: 3609

Direction of rotation: both directions Indexing: hydromechanical

Operation with foot pedal

Weight: 23 kg

Maximum admissible load

According to the version without indexing (see page 2)

Maximum admissible torque around the rotation axis Mz

The maximum torque around the rotation axis of the rotating module M_Z in engaged mode is 800 Nm.

In the case of eccentric loads, it is recommended to compensate these by counterweights. In offposition the indicated maximum torques may

The forces and torques have to be considered by the operator.

Accessories

Adaptor plate

for vertical mounting of the rotating module

Part no. 6311326

See data sheet M 8.110

Flange plate

round for individual fixing holes


Part no. 6311 400

See data sheet M 8.120

259

The rotating module and the indexing unit including hydraulic hose and hydraulic oil are delivered as completely assembled unit ready for use.

Operating angle



-4x M10 x 18 deep

Dimensions